

The Imaging Source Helpdesk

[知识库](#) > [Software](#) > [Software for Linux](#) > [USB3Vision instead of V4L2 for USB cameras](#)

USB3Vision instead of V4L2 for USB cameras

S.Geißler - 2020-02-10 - [Software for Linux](#)

V4L2 has limitations in stepping of frame rates and video formats. Our USB 3.3 and above cameras implement USB3Vision. This can be used by the Aravis library. Then many more video formats and frame rates are available.

For doing so, you checkout the development branch of tiscamera. Then you need to run cmake again, build and install tiscamera. In the terminal enter:

```
cd tiscamera/build
cmake -DBUILD_ARAVIS=ON -DBUILD_TOOLS=ON -DTCAM_ARAVIS_USB_VISION=ON ..
make -j 16
sudo make install
```

If you run `tcam-ctrl -l`, then your camera should be listed as "Aravis" instead of "v4l2" device.

Keywords: Linux, video formats, frame rate, driver, v4l2, Aravis and USB